

G-13.mft



validates all coins safely and reliably



secure

- high quality coin validation using Multi-Frequency-Technology
- detection of coin material by three coil pairs together with proven optical diameter measurement
- simultaneous evaluation of 24 measurement parameters for 2 x 16 coin channels
- protection against string manipulation
- optical monitoring of coin path

flexible

- configuration and data block download via well-known WinEMP software
- inhibit of single coins or coin groups via DIL switch
- teach function for up to 6 tokens as standard


versatile

machine interfaces available

- serial S1
- serial MDB
- ccTalk, also via USB connection
- parallel, also binary or serial impulses
- SGI (Simple Gaming Interface) with fast coin acceptance for Casino applications

Accessories

- midi and mini front plate
- wake-up sensor for low-power applications
- 3-way sorter Standard
- 3-way High Speed Sorter HSD 3000



Technical data

Height	102 mm
Width	89 mm
Depth	52 mm
Coin diameter	1.5 - 31.5 mm (option up to 32.5 mm)
Coin thickness	1.5 - 2.5 mm (option up to 3.3 mm)
Temperature	0°C - 60°C (option: -25 up to +70°C)
Power supply:	10 - 24 V DC (optional: 10 - 48 VDC)